## Installation

This diffuser sample is designed using a two-way pattern for uniform distribution of input waves on each axis. Two different depths in Logan slices allow it to operate in the broadband frequency range, especially at lower frequencies, and features such as improved low frequency response, echo control, dramatic reflection control and field point distribution. Have a focal point between the speakers known as the "Sweet spot". The scattering range is from 350 Hz to 6000 Hz. Logan consists of compressed ionolite (EPS) with polyurethane-painted wood veneer, a high-quality high-performance inspiration panel for the Hi-Fi environment, home







